



# Universal Oven Seal

## 4 Sided Seal



### Fitting the new seal

- 1) Measure the distance between the holes.
- 2) Cut the top, bottom and sides of the seal in accordance with the following table. This will allow for stretching.

| DISTANCE BETWEEN THE HOLES | SHORTEN THE SEAL BY -    |
|----------------------------|--------------------------|
| 250 - 350mm                | 20mm                     |
| 351 - 400mm                | 25mm                     |
| 401 - 450mm                | 30mm                     |
| For every additional 50mm  | Shorten by a further 5mm |

- 3) Trim the top and bottom corners to an angle of 45 degrees
- 4) Insert the barbed corner hooks into the slot of the seal.  
The hooks must face the oven.
- 5) Stretch and clip the seal into the holes.